Ultra96 USB-to-JTAG/UART Pod




GETTING STARTED:

- 1. The Ultra96 USB-to-JTAG/UART Pod ships with pre-programmed firmware that allows the JTAG interface to be recognized by Xilinx Vivado software.
- 2. Additionally, most host machines will also automatically install the driver for the Serial Terminal interface.
- 3. Connect the Pod into the Ultra96 by aligning the following: a. JTAG: Pod J2 with Ultra96 J2
 - b LIART: Pod .13 with Ultra96.16
- 4. Plug a microUSB cable between the Pod's microUSB Port (J1) and a host computer.
- 5. If the serial terminal drivers do not automatically install, you can manually install the driver for the FT2232H device. Visit ftdichip.com/Drivers/VCP.htm then download and install the appropriate driver for your operating system.
- 6. To easily test both the JTAG and UART capabilities, follow Tutorials 01 and 02 for the Ultra96 at avnet.me/Ultra96tutorials.

Features

- microUSB high-speed USB 2.0 connection
- Female UART header compatible with the Ultra96 UART male header
- Female JTAG header compatible with the Ultra96 JTAG male header







^{*}The Ultra96 USB-to-JTAG/UART Pod is designed for product evaluation at research and development facilities by trained professionals. The board included in the kit is not intended for production use.

AVNET DESIGN KIT LICENSE AND PRODUCT WARRANTY

- THE AVNET DESIGN KIT ("DESIGN KIT" OR "PRODUCT") AND ANY SUPPORTING DOCUMENTATION ("DOCUMENTATION" OR "PRODUCT DOCUMENTATION") IS SUBJECT TO THIS LICENSE AGREEMENT ("LICENSE"). USE OF THE PRODUCT OR DOCUMENTATION SIGNIFIES ACCEPTANCE OF THE TERMS AND CONDITIONS OF THIS LICENSE. THE TERMS OF THIS LICENSE AGREEMENT ARE IN ADDITION TO THE AVNET CUSTOMER TERMS AND CONDITIONS, WHICH CAN BE VIEWED AT WWW. AWNET.COM. THE TERMS OF THIS LICENSE AGREEMENT WILL CONTROL IN THE EVENT OF A CONFLICT.
- Limited License. Avnet grants You, the Customer, ("You" or "Customer") a limited, non-exclusive, non-transferable, license to: (a) use the
 Product for Your own internal testing, evaluation and design efforts at a single Customer site; (c) make, use and sell the Product in a single production
 unit. No other rights are granted and Avnet and any other Product licensor reserves all rights not specifically granted in this License Agreement.
 Except as expressly permitted in this License, neither the Design Kit, Documentation, nor any portion may be reverse engineered, disassembled,
 decompiled, sold, donated, shared, leased, assigned, sublicensed or otherwise transferred by Customer. The term of this License is in effect until
 terminated. Customer may terminate this license at any time by destroying the Product and all copies of the Product Documentation.
- Changes. Avnet may make changes to the Product or Product Documentation at any time without notice. Avnet makes no commitment to update
 or upgrade the Product or Product Documentation and Avnet reserves the right to discontinue the Product or Product Documentation at any time
 without notice.
- Product Documentation. Product Documentation is provided by Awnet on an "AS-IS" basis and does not form a part of the properties of the Product.
 All Product Documentation is subject to change without notice. Awnet makes no representation as to the accuracy or completeness of the Product
 Documentation, and DISCLAIMS ALL REPRESENTATIONS, WARRANTIES AND LIABILITIES UNDER ANY THEORY WITH RESPECT TO PRODUCTI INFORMATION.
- 4. Limited Product Warranty, AWIET WARRANTS THAT AT THE TIME OF DELIVERY, THE PRODUCTS SHALL MEET THE SPECIFICATIONS STATED IN AWIET DOCUMENTATION FOR SIXTY (60) DAYS FROM DELIVERY OF PRODUCTS. IF THE CUSTOMER CAN PROVIDE PROOF THAT THE QUALIFIED AWNET PRODUCT WAS PURCHASED FOR THE PURPOSE OF AND DEPLOYED AS A COMPONENT IN THE CUSTOMER'S COMMERCIALLY AWAILABLE PRODUCT THE WARRANTY WILL BE EXTENDED TO TWELVE (12) MONTHS FROM THE DATE OF PURCHASE. TO THE EXTENT PERMITTED BY LAW, AWNET MAKES NO OTHER WARRANTY EXPRESS OR INVEILED, SUCH AS WARRANTY OF MERCHANTABILITY, FITNESS FOR PURPOSE OR NON-INFRINGEMENT, YOUR SOLE AND EXCLUSIVE REMEDY FOR BREACH OF AWNETS WARRANTY IS, AT AWNETS CHOICE: (I) REPAIR THE PRODUCTS; (II) REPLACE THE PRODUCTS AT NO COST TO YOU: OR (III) REPURL OVER THE PRODUCTS AT NO COST
- 5. IMITATIONS OF LIABILITY CUSTOMER SHALL NOT BE ENTITLED TO AND AVNET WILL NOT LIABLE FOR ANY INDIRECT. SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES FOR ANY KIND OR NATURE, INCLUDING, WITHOUT IMITATION, BUSINESS INTERRUPTION COSTS, LOSS OF PROPERT OR REVENUE, LOSS OF DATA, PROMOTIONAL OR MANUFACTURING EXPENSES, OVERHEAD, COSTS OR EXPENSES ASSOCIATED WITH WARRANTY OR INTELLECTUAL PROPERTY INFRINGEMENT CLAIMS, INJURY TO REPUTATION OR LOSS OF CUSTOMERS, EVEN IF AWNET HAS BEEN ADVISED OF POSSIBILITY OF SUCH DAWAGES. THE PRODUCTS AND DOCUMENTATION ARE NOT DESIGNED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN MEDICAL, MILITARY, AIR CRAFT, SPACE OR LIFE SUPPORT EQUIPMENT NOR IN APPLICATIONS WHERE FAILURE OR MALFUNCTION OF THE PRODUCTS CAN REASONABLY BE EXPECTED TO RESULT IN A PRESONAL INJURY, DEATH OR SEVERE PROPERTY OR ENVIRONITUAL DAMAGE. INCLUSION OR USE OF PRODUCTS IN SUCH EQUIPMENT OR APPLICATIONS, WITHOUT PRIOR AUTHORIZATION IN WRITING OF AWNET, IS NOT PERMITTED AND IS AT CUSTOMER'S OWN RISK. CUSTOMER'S GOVERNIES.
- 6. LIMITATION OF DAMAGES, CUSTOMER'S RECOVERY FROM AVNET FOR ANY CLAIM SHALL NOT EXCEED CUSTOMER'S PURCHASE PRICE FOR THE PRODUCT GIVING RISE TO SUCH CLAIM IRRESPECTIVE OF THE NATURE OF THE CLAIM, WHETHER IN CONTRACT, TORT, WARRANTY, OR OTHERWISE.
- INDEMNIFICATION, AVNET SHALL NOT BE LIABLE FOR AND CUSTOMER SHALL INDEMNIFY, DEFEND AND HOLD AVNET HARMLESS FROM ANY CLAIMS
 BASED ON AVNET'S COMPLIANCE WITH CUSTOMER'S DESIGNS, SPECIFICATIONS OR INSTRUCTIONS, OR MODIFICATION OF ANY PRODUCT BY PARTIES
 OTHER THAN AVNET, OR USE IN COMBINATION WITH OTHER PRODUCTS.
- 8. U.S. Government Restricted Rights. The Product and Product Documentation are provided with "RESTRICTED RIGHTS." If the Product and Product Documentation and related technology or documentation are provided to or made available to the United States Government, any use, duplication, or disclosure by the United States Government is subject to restrictions applicable to proprietary commercial experts produced as set forth in FAR 52.227-14 and DFAR 252.227-7013, et seq., its successor and other applicable laws and regulations. Use of the Product by the United States Government constitutes acknowledgment of the proprietary rights of Avnet and any third parties. No other governments are authorized to use the Product without written agreement of Avnet and applicable third parties.
- Ownership. Licensee acknowledges and agrees that Avnet or Avnet's licensors are the sole and exclusive owner of all intellectual Property Rights in the Licensed Materials, and Licensee shall acquire no right, title, or interest in the Licensed Materials, other than any rights expressly granted in this Agreement.
- 10. Intellectual Property. All trademarks, service marks, logos, slogans, domain names and trade names (collectively "Marks") are the properties of their respective owners. Arnet disclaims any proprietary interest in Marks other than its own. Awnet and AV design logos are registered trademarks and service marks of Awnet, Inc., Awnet's Marks may be used only with the prior witten permission of Awnet. Inc.
- 11. General. The terms and conditions set forth in the License Agreement or at www.avnet.com will apply notwithstanding any conflicting, contrary or additional terms and conditions in any purchase order, sales acknowledgement confirmation or other document there is any conflicting, the terms of this License Agreement will control. This License may not be assigned by Customer, by operation of law, merger or otherwise, without the prior written consent of Avnet and any attempted or purported assignment shall be void. Licensee understands that portions of the Licensed Materials may have been licensed to Avnet from third parties and that such third parties are intended beneficiaries of the provisions of this Agreement. In the event any of the provisions of this Agreement are for any reason determined to be void or unenforceable, the remaining provisions will remain in full effect. This constitutes the entire agreement between the parties with respect to the use of this Product, and superseids all prior or contemporaneous understandings or agreements, written or oral, regarding such subject matter. No waiver or modification is effective unless agreed to in writing and signed by authorized representatives of both parties. The obligations, rights, terms and conditions shall be binding on the parties and their respective successors and assigns. The License Agreement is governed by and construed in accordance with the laws of the State of Arrison excluding any law or principle, which would apply the law of any other jurisdiction. The United Nations Convention for the International Sale of Goods shall not apply.

Copyright © 2018 Avnet, Inc. AVNET, "Reach Further," and the Avnet logo are registered trademarks of Avnet, Inc. All other brands are the property of their respective owners. LIT# 5362-QSC-AES-ACC-U96-JTAG-V1