

Model Name		RNUC15CRHC70000U	
ASUS® NUC 15 Pro Tall Barebone Kit			
OS		Supports Windows 11 Home/Pro/IoT Enterprise, RedHat Enterprise Linux, Ubuntu	W/O OS
CPU		Intel® Core™ 7 240H Processor (24M Cache, P-core up to 5.20 GHz / E-core up to 4.00 GHz)	cTDP 45W
NPU		n/a	
Chipset		Integrated - Intel® SoC	
Graphics		Integrated - Intel® Graphics	
Memory	Installed	n/a	
	Supported	2 x SO-DIMM DDR5-6400/5600MHz* memory slots *CSO-DIMM only for 6400MHz	Max. 96GB
Storage	Installed	n/a	
	Supported	1 x M.2 2280 PCIe Gen4x4 NVMe™ SSD (supports 128GB ~ 8TB PCIe Gen5 ready) 1 x M.2 2242 PCIe Gen4x4 NVMe™ SSD (supports 128GB ~ 2TB)	Key type M Key type M
Wireless Network		Intel® Wi-Fi 7 BE202 (Gig+), 2x2, and Bluetooth® 5.4	(M.2 2230)
LAN		1 x Intel® i226-V LAN (10/100/1000/2500 Mbps)	2.5 GbE
Wake-on-LAN Support		Wake on from S5 & Modern Standby	
Optical Drive		n/a	
Integrated Speaker		n/a	
Audio		Up to 7.1 multichannel (or 8-channel) digital audio on HDMI and DP Type-C ports	
Card Reader		n/a	
TPM		fTPM 2.0 (Intel PTT)	
HDMI CEC	Onboard	Yes, 2 ports on back panel	
Interface	Front I/O	1 x USB 3.2 Gen2x2 Type-C (5V/3A, 20Gbps) 2 x USB 3.2 Gen2 Type-A (5V/0.9A, 10Gbps)	
	Side I/O	1 x Kensington Lock Slot	
	Rear I/O	2 x Thunderbolt™ 4 (with DP2.1 & USB4 5V/3A, 40Gbps) 1 x USB 3.2 Gen2 Type-A (5V/0.9A, 10Gbps) 1 x USB 2.0 Type-A (5V/0.5A, 480Mbps) 2 x HDMI 2.1 (with TMDS, up to 4K@60Hz) 1 x Intel® 2.5G LAN (RJ45) 1 x Cable Locking Arm 1 x DC-in <i>Supports up to four 4K@60Hz displays simultaneously (2 x HDMI + 2 x TBT4)</i>	
Physical	Dimensions	4.61" x 4.41" x 2.13" 117 x 112 x 54mm	(0.7L)
	Weight	0.80 lbs. 0.364 kg	
Power Supply		120W Power Adapter (19V _{DC} / 6.32A)	
Power Cord		US AC Cord (IEC C5)	
Accessories		VESA Mount & Screws / AC Power Adapter / Power Cord	