


GB60



BENEFITS

- 60W Convection Cooled
- Power density is more than 25% higher than other 2"X3" products
- Wide temperature range of -10°C to +80°C
- Level V Efficiency Compliant Models
- 6.67 Watts/IN³ power density @70°C
- Does not require a heating element to turn on at -40°C

FEATURES

- Optional Power ON LED
- RoHS Compliant
- Approved to CSA/EN/IEC/UL60950-1, 2nd Edition

VALUE PROPOSITION

- The smallest convection cooled 60W power supply in its class.
- Reliably delivers 40W at 70°C without the need for a fan. Reducing total application cost.
- Does not require a heating element at -40°C saving \$2 to \$10 per unit and improving end application efficiency.
- High convection rating minimizes the need to rely on forced air, thereby increasing reliability and minimizing system cost by eliminating the need for a fan.
- SL Power local technical support capabilities provide real time help in solving potential design problems which could otherwise cause revenue loss due to delays in end product introduction.
- Extensive global presence can support customers product needs as they migrate from development to production, frequently in multiple locations around the world.

MARKETS

PLATFORMS

APPLICATIONS



Test & Measurement

TEST & MEASUREMENTS

- Electronic Test
- Analytical Test



LED

LED

- Lighting



Automation

AUTOMATION

- Robotics
- Instrumentation



ITE & Comms

ITE & COMMS

- Datacom

TEST & MEASUREMENTS

- Network Analyzers
- Chemistry Analyzers

LED

- Theater Lighting
- Low Voltage LED Lighting

AUTOMATION

- Factory Automation
- Process Control

ITE & COMMS

- Multiplexers
- High End Routers

