

| | | | | |
|--|--|-----------------|--|--|
| Product description: | TFT-LCD Module | Model name: | G084SN05 V7 | |
| AUO Part No.: | 97.08G01.701-S06 | Product weight: | 260g | |
| Substance identification | | Exist? (Yes/No) | Description of use | THE WEIGHT (mg) OF THE RELATED MATERIAL (using the SVHC) |
| Substance name | (CAS No) | | | |
| 4,4'-Diaminodiphenylmethane (MDA) | 101-77-9 | No | | |
| 5-tert-butyl-2,4,6-trinitro-m-xylene(musk xylene) | 81-15-2 | No | | |
| Alkanes, C10-13, chloro (Short Chain Chlorinated Paraffins) | 85535-84-8 | No | | |
| Anthracene | 120-12-7 | No | | |
| Benzyl butyl phthalate (BBP) | 85-68-7 | No | | |
| Bis(2-ethylhexyl)phthalate | 117-81-7 | No | | |
| Bis(tributyltin) oxide (TBTO) | 56-35-9 | No | | |
| Cobalt dichloride | 7646-79-9 | No | | |
| Diarsenic pentaoxide | 1303-28-2 | No | | |
| Diarsenic Trioxide | 1327-53-3 | No | | |
| Dibutyl phthalate (DBP) | 84-74-2 | No | | |
| Hexabromocyclododecane and all major diastereoisomers identified | 25637-99-4 and 3194-55-6 | No | | |
| alpha-hexabromocyclododecane | 134237-50-6 | | | |
| beta-hexabromocyclododecane | 134237-51-7 | | | |
| Lead Hydrogen Arsenate | 134237-52-8 | | | |
| | 7784-40-9 | No | | |
| Sodium dichromate | 10588-01-9 (anhydrous) | No | | |
| | 7789-12-0 (dihydrate) | | | |
| Triethyl arsenate | 15606-95-8 | No | | |
| 2,4 - Dinitrotoluene | 121-14-2 | No | | |
| Aluminosilicate Refractory Ceramic Fibres Al2O3: 43.5 – 47 % w/w, and SiO2: 49.5 – 53.5 % w/w or Al2O3: 45.5 – 50.5 % w/w, and SiO2: 48.5 – 54 % w/w | - | No | | |
| Anthracene oil | 90640-80-5 | No | | |
| Anthracene oil, anthracene-low | 90640-82-7 | No | | |
| Anthracene oil, anthracene paste | 90640-81-6 | No | | |
| Anthracene oil, anthracene paste, anthracene fraction | 91995-15-2 | No | | |
| Anthracene oil, anthracene paste, distn. lights | 91995-17-4 | No | | |
| Diisobutyl phthalate | 84-69-5 | No | | |
| Lead chromate | 7758-97-6 | No | | |
| Lead chromate molybdate sulphate red (C.I.Pigment Red 104) | 12656-85-8 | No | | |
| Lead sulfochromate yellow (C.I. Pigment Yellow 34) | 1344-37-2 | No | | |
| Coal tar pitch, high temperature | 65996-93-2 | No | | |
| Tris (2-chloroethyl) phosphate | 115-96-8 | No | | |
| Aluminosilicate Refractory Ceramic Fibres (a)Al2O3, SiO2 and ZrO2 are present within the following concentration ranges: · Al2O3: 35 – 36 % w/w, and · SiO2: 47.5 – 50 % w/w, and | - | No | | |
| Acrylamide | 79-06-1 | No | | |
| Trichloroethylene | 79-01-6 | No | | |
| Boric acid | 10043-35-3 (11113-50-1) | Yes | FLM_POL_C/PVA & FLM_POL_A/PVA (It is a additive volume, not equals residual.) (The crosslinking agent of PVA) | 42.04 |
| Disodium tetraborate, anhydrous | 1330-43-4, (anhydrous) 12179-04-3, (pentahydrate) 1303-96-4, (decahydrate) | Yes | FLM_POL_C/PVA; FLM_POL_A/PVA; (It is a additive volume, not equals residual.) (The crosslinking agent of PVA) | 34.251 |
| Tetraboron disodium heptaoxide, hydrate | 12267-73-1 | No | | |
| Potassium Dichromate | 7778-50-9 | No | | |
| Ammonium Dichromate | 7789-00-6 | No | | |
| Potassium Chromate | 7789-00-6 | No | | |
| Sodium Chromate | 7775-11-3 | No | | |
| Cobalt(II) sulphate | 10124-43-3 | No | | |
| Cobalt(II) dinitrate | 10141-05-6 | No | | |
| Cobalt(II) carbonate | 513-79-1 | No | | |
| Cobalt(II) diacetate | 71-48-7 | No | | |
| 2-Methoxyethanol | 109-86-4 | No | | |
| 2-Ethoxyethanol | 110-80-5 | No | | |
| Chromium trioxide | 1333-82-0 | No | | |
| Acids generated from chromium trioxide and their oligomers: | 7738-94-5 13530-68-2 - | No | | |

Remark:

Company Name: AU Optronics Corp.

Company Address: 1 Li-Jsin Rd. 2 Hsinchu Science Park, Hsinchu 300, Taiwan, R.O.C

AUO Contact window: Jerry HOM Chen

Phone: +886-3-500-8800

Email: JerryHOM.Chen@auo.com

Date: 2011/10/21