



# REACH SVHC Survey Summary

保管單位 Storage	GERM
保存年限 Retention Period	五年 5 years

<b>Product description:</b>	TFT-LCD Module	<b>Model name:</b>	G150XG03 V2	
<b>AUO Part No.:</b>	97.15G05.202-S01	<b>Product weight:</b>	1150 g	
Substance identification		Exist? (Yes/No)	Description of use	THE WEIGHT (mg) OF THE RELATED MATERIAL (using the SVHC)
Substance name	(CAS No)			
4,4'-Diaminodiphenylmethane (MDA)	101-77-9	No		
5-tert-butyl-2,4,6-trinitro-m-xylene(musk xylene)	81-15-2	No		
Alkanes, C10-13, chloro (Short Chain Chlorinated Paraffins)	85535-84-8	No		
Anthracene	120-12-7	No		
Benzyl butyl phthalate (BBP)	85-68-7	No		
Bis(2-ethylhexyl)phthalate	117-81-7	No		
Bis(tributyltin) oxide (TBTO)	56-35-9	No		
Cobalt dichloride	7646-79-9	No		
Diarsenic pentaoxide	1303-28-2	No		
Diarsenic Trioxide	1327-53-3	No		
Dibutyl phthalate (DBP)	84-74-2	No		
Hexabromocyclododecane and all major diastereoisomers identified	25637-99-4 and 3194-55-6	No		
alpha-hexabromocyclododecane	134237-50-6			
beta-hexabromocyclododecane	134237-51-7			
Lead Hydrogen Arsenate	134237-52-8	No		
Sodium dichromate	7784-40-9	No		
Triethyl arsenate	10588-01-9 (anhydrous) 7789-12-0 (dihydrate)	No		
2,4 - Dinitrotoluene	15606-95-8	No		
Aluminosilicate Refractory Ceramic Fibres Al2O3: 43.5 – 47 % w/w, and SiO2: 49.5 – 53.5 % w/w or Al2O3: 45.5 – 50.5 % w/w, and SiO2: 48.5 – 54 % w/w	121-14-2	No		
Anthracene oil	-	No		
Anthracene oil, anthracene-low	90640-80-5	No		
Anthracene oil, anthracene paste	90640-82-7	No		
Anthracene oil, anthracene paste, anthracene fraction	90640-81-6	No		
Anthracene oil, anthracene paste, distn. lights	91995-15-2	No		
Diisobutyl phthalate	91995-17-4	No		
Lead chromate	84-69-5	No		
Lead chromate molybdate sulphate red (C.I.Pigment Red 104)	7758-97-6	No		
Lead sulfochromate yellow (C.I. Pigment Yellow 34)	12656-85-8	No		
Coal tar pitch, high temperature	1344-37-2	No		
Tris (2-chloroethyl) phosphate	65996-93-2	No		
Aluminosilicate Refractory Ceramic Fibres (a)Al2O3, SiO2 and ZrO2 are present within the following concentration ranges: · Al2O3: 35 – 36 % w/w, and · SiO2: 47.5 – 50 % w/w, and	115-96-8	No		
Acrylamide	-	No		
Trichloroethylene	79-06-1	No		
Boric acid	79-01-6	No		
	10043-35-3 (11113-50-1)	Yes	FLM_POL_C/PVA & FLM_POL_A/PVA (It is a additive volume, not equals residual.) (The crosslinking agent of PVA)	165.88
Disodium tetraborate, anhydrous	1330-43-4, (anhydrous) 12179-04-3, (pentahydrate) 1303-96-4, (decahydrate)	Yes	FLM_POL_C/PVA & FLM_POL_A/PVA (It is a additive volume, not equals residual.) (The crosslinking agent of PVA)	135.14
Tetraboron disodium heptaoxide, hydrate	12267-73-1	No		
Potassium Dichromate	7778-50-9	No		
Ammonium Dichromate	7789-00-6	No		
Potassium Chromate	7789-00-6	No		
Sodium Chromate	7775-11-3	No		
Cobalt(II) sulphate	10124-43-3	No		



# REACH SVHC Survey Summary

保管單位 Storage	GERM
保存年限 Retention Period	五年 5 years

<b>Product description:</b>	TFT-LCD Module	<b>Model name:</b>	G150XG03 V2	
<b>AUO Part No.:</b>	97.15G05.202-S01	<b>Product weight:</b>	1150 g	
Substance identification		Exist? (Yes/No)	Description of use	THE WEIGHT (mg) OF THE RELATED MATERIAL (using the SVHC)
Substance name	(CAS No)			
Cobalt(II) dinitrate	10141-05-6	No		
Cobalt(II) carbonate	513-79-1	No		
Cobalt(II) diacetate	71-48-7	No		
2-Methoxyethanol	109-86-4	No		
2-Ethoxyethanol	110-80-5	No		
Chromium trioxide	1333-82-0	No		
Acids generated from chromium trioxide and their oligomers	7738-94-5 13530-68-2 -	No		
2-ethoxyethyl acetate	111-15-9	No		
strontium chromate	7789-06-2	No		
1,2-Benzenedicarboxylic acid, di-C7-11-branched and linear	68515-42-4	No		
Hydrazine	7803-57-8, 302-01-2	No		
1-methyl-2-pyrrolidone	872-50-4	No		
1,2,3-trichloropropane	96-18-4	No		
1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters	71888-89-6	No		
Dichromium tris(chromate)	24613-89-6	No		
Potassium hydroxyoctaoxodizincatedichromate	11103-86-9	No		
Pentazinc chromate octahydroxide	49663-84-5	No		
Aluminosilicate Refractory Ceramic Fibres (Sixth list of SVHC)	—	No		
Zirconia Aluminosilicate Refractory Ceramic Fibres (Sixth list of SVHC)	—	No		
Formaldehyde, oligomeric reaction products with aniline	25214-70-4	No		
Bis(2-methoxyethyl)phthalate	117-82-8	No		
2-Methoxyaniline; o-Anisidine	90-04-0	No		
4-(1,1,3,3-tetramethylbutyl)phenol	140-66-9	No		
1,2-dichloroethane	107-06-2	No		
Bis(2-methoxyethyl) ether	111-96-6	Yes	Color Filter/Photo Spacer	10.04
Arsenic acid	7778-39-4	No		
Calcium arsenate	7778-44-1	No		
Trilead diarsenate	3687-31-8	No		
N,N-dimethylacetamide	127-19-5	No		
2,2'-dichloro-4,4'-methylenedianiline	101-14-4	No		
Phenolphthalein	77-09-8	No		
Lead diazide; Lead azide	13424-46-9	No		
Lead styphnate	15245-44-0	No		
Lead dipicrate	6477-64-1	No		

Remark:

Company Name: AU Optronics Corp.

Company Address: 1 Li-Jsin Rd. 2 Hsinchu Science Park, Hsinchu 300, Taiwan, R.O.C

AUO Contact window: Maggie.PT.Li

Phone: +886-3-500-8800

Email: Maggie.PT.Li@auo.com

Date: 2012/07/03