



REACH SVHC Survey Summary

保管單位 Storage	GERM
保存年限 Retention Period	五年 5 years

Product description:	TFT-LCD Module	Model name:	G121XN01 V0	
AUO Part No.:	97.12G02.000-S01	Product weight:	495 g	
Substance identification		Exist? (Yes/No)	Description of use	THE WEIGHT (mg) OF THE RELATED MATERIAL (using the SVHC)
Substance name	(CAS No)			
4,4'-Diaminodiphenylmethane (MDA)	101-77-9	No		
5-tert-butyl-2,4,6-trinitro-m-xylene(musk xylene)	81-15-2	No		
Alkanes, C10-13, chloro (Short Chain Chlorinated Paraffins)	85535-84-8	No		
Anthracene	120-12-7	No		
Benzyl butyl phthalate (BBP)	85-68-7	No		
Bis(2-ethylhexyl)phthalate	117-81-7	No		
Bis(tributyltin) oxide (TBTO)	56-35-9	No		
Cobalt dichloride	7646-79-9	No		
Diarsenic pentaoxide	1303-28-2	No		
Diarsenic Trioxide	1327-53-3	No		
Dibutyl phthalate (DBP)	84-74-2	No		
Hexabromocyclododecane and all major diastereoisomers identified	25637-99-4 and 3194-55-6	No		
alpha-hexabromocyclododecane	134237-50-6			
beta-hexabromocyclododecane	134237-51-7			
Lead Hydrogen Arsenate	134237-52-8	No		
Sodium dichromate	7784-40-9	No		
	10588-01-9 (anhydrous)	No		
	7789-12-0 (dihydrate)	No		
Triethyl arsenate	15606-95-8	No		
2,4 - Dinitrotoluene	121-14-2	No		
Aluminosilicate Refractory Ceramic Fibres Al2O3: 43.5 – 47 % w/w, and SiO2: 49.5 – 53.5 % w/w or Al2O3: 45.5 – 50.5 % w/w, and SiO2: 48.5 – 54 % w/w	-	No		
Anthracene oil	90640-80-5	No		
Anthracene oil, anthracene-low	90640-82-7	No		
Anthracene oil, anthracene paste	90640-81-6	No		
Anthracene oil, anthracene paste, anthracene fraction	91995-15-2	No		
Anthracene oil, anthracene paste, distn. lights	91995-17-4	No		
Diisobutyl phthalate	84-69-5	No		
Lead chromate	7758-97-6	No		
Lead chromate molybdate sulphate red (C.I.Pigment Red 104)	12656-85-8	No		
Lead sulfochromate yellow (C.I. Pigment Yellow 34)	1344-37-2	No		
Coal tar pitch, high temperature	65996-93-2	No		
Tris (2-chloroethyl) phosphate	115-96-8	No		
Aluminosilicate Refractory Ceramic Fibres (a)Al2O3, SiO2 and ZrO2 are present within the following concentration ranges: · Al2O3: 35 – 36 % w/w, and · SiO2: 47.5 – 50 % w/w, and	-	No		
Acrylamide	79-06-1	No		
Trichloroethylene	79-01-6	No		
Boric acid	10043-35-3 (11113-50-1)	Yes	FLM_POL_C/PVA & FLM_POL_A/PVA (It is a additive volume, not equals residual.) (The crosslinking agent of PVA)	1040.83
Disodium tetraborate, anhydrous	1330-43-4, (anhydrous) 12179-04-3, (pentahydrate) 1303-96-4, (decahydrate)	No		
Tetraboron disodium heptaoxide, hydrate	12267-73-1	No		
Potassium Dichromate	7778-50-9	No		
Ammonium Dichromate	7789-00-6	No		
Potassium Chromate	7789-00-6	No		
Sodium Chromate	7775-11-3	No		
Cobalt(II) sulphate	10124-43-3	No		
Cobalt(II) dinitrate	10141-05-6	No		



REACH SVHC Survey Summary

保管單位 Storage	GERM
保存年限 Retention Period	五年 5 years

Product description:	TFT-LCD Module	Model name:	G121XN01 V0	
AUO Part No.:	97.12G02.000-S01	Product weight:	495 g	
Substance identification		Exist? (Yes/No)	Description of use	THE WEIGHT (mg) OF THE RELATED MATERIAL (using the SVHC)
Substance name	(CAS No)			
Cobalt(II) carbonate	513-79-1	No		
Cobalt(II) diacetate	71-48-7	No		
2-Methoxyethanol	109-86-4	No		
2-Ethoxyethanol	110-80-5	No		
Chromium trioxide	1333-82-0	No		
Acids generated from chromium trioxide and their oligomers:	7738-94-5 13530-68-2 -	No		

Remark:

Company Name: AU Optronics Corp.
Company Address: 1 Li-Jsin Rd. 2 Hsinchu Science Park, Hsinchu 300, Taiwan, R.O.C

AUO Contact window: Maggie PT Li
Phone: +886-3-500-8800
Email: Maggie.PT.Li@auo.com
Date: 2012/01/20