

15KW 3 ϕ 4W Input With High Voltage Output

RST-15K-HV series

— Dir	ne	nsio			
L	*	W	*	Н	
540	*	424	*	83.5(2U)	mm
21.3	*	16.7	*	3.29(2U)	inch





Front





Parallel (PC	c FL us	TOWNERSE EXEMPLESEE	EAE	СВ	CE	UK CA
	UL62368-1	BS EN/EN62368-1	TPTC004	IEC62368-1		

Features

- 3 ψ 3-wire / \triangle 196~305VAC or 3 ψ 4-wire / Y 340~530VAC
- High efficiency up to 94%
- · Forced air cooling
- · Output voltage and constant current level programmable
- Wide voltage adjustment range 1~120%
- · Active current sharing up to 2 units(28.5KW)
- Built-in remote ON-OFF control / Alarm signal
- Protections: Short circuit / Overload / Over voltage / Over temperature / Fan fail
- 5 years warranty



Applications

- Energy & power system
- · U.V or laser diode application
- · Electrolysis system
- · Factory control or automation apparatus
- · Burn-in facility
- · RF application
- EV charging station

GTIN CODE MW Search: <u>https://www.meanwell.com/serviceGTIN.aspx</u>

Description

RST-15K-HV is a 15KW 3 ϕ input enclosed type AC/DC power supply. This series operates for the wide range three phase AC input and offers the models with the high voltage DC output(115V/230V/380V) that mostly demanded from the industry. This series provides models with forced air cooling, that can be working at ambient temperature up to 70°C. Moreover, RST-15K-HV provides vast design flexibility by equipping various built-in functions such as the output programming, active current sharing, remote ON-OFF control, alarm signals.....etc.





SPECIFICATION

	RST-15K-115	RST-15K-230	RST-15K-380				
DC VOLTAGE (factory default)	115V	230V	380V				
	130A	64.8A	39.55A				
	0 ~ 130A	0~69A	0~45A				
			15030W				
			334 ~ 400V				
			4Vp-p				
RIFFLE & NOISE (IIIax.) Note.2							
VOLTAGE ADJ. RANGE		170~260V	260 ~ 400V				
			1.1.00/				
			±1.0%				
			±0.5%				
LOAD REGULATION	±0.5%	±0.5%					
SETUP, RISE TIME	3000ms, 200ms at full load						
HOLD UP TIME (Typ.)	16ms 230VAC/400VAC at 75% load	10ms / 230VAC/400VAC at full load					
VOLTAGE RANGE	3 ₺ 3W/△196~305VAC or 3 ₺ 4W/Y 340~530VAC						
FREQUENCY RANGE	47 ~ 63Hz						
POWER FACTOR (Typ.)	≥0.98/230VAC(400VAC)/≥0.97/277VAC	(480VAC) at full load					
EFFICIENCY (Typ.) Note.7	93%	94%	94%				
AC CURRENT (Typ.)	45A/230VAC(3 ψ 3-wire / \triangle) 26A/4	400VAC(3 & 4-wire / Y)	I				
		, ,					
	· · · · · ·						
OVERLOAD		unit will abutdown ofter 5 and re newer on to	F0.001/0F				
	· · · ·						
OVER VOLTAGE			420 ~ 480V				
		, , ,					
	•						
CONSTANT CURRENT LEVEL PROGRAMMABLE		wable between 20 ~ 100% of rated current. P	lease refer to the Function Manual				
REMOTE ON-OFF CONTROL	Please refer to the Function Manual						
ALARM SIGNAL OUTPUT	AC fail, DC OK, fan fail, OTP. Please refer	to the Function Manual.					
WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")						
WORKING HUMIDITY	20 ~ 90% RH non-condensing						
STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH non-condensing	q					
		h along X Y Z axes					
		• • •	proved				
			ploved				
ISOLATION RESISTANCE Note.4	, ,		Teat Level / Nata				
			Test Level / Note				
EMC EMISSION							
	Voltage Flicker	BS EN/EN61000-3-3					
	BS EN/EN55024 , BS EN/EN61204-3, BS	EN/EN61000-6-2					
	Parameter	Standard	Test Level / Note				
	ESD	BS EN/EN61000-4-2	Level 3, 8KV air ; Level 2, 4KV contact				
	Radiated	BS EN/EN61000-4-3	Level 3				
	EET / Buret	BS EN/EN61000-4-4	Level 3				
EMC IMMUNITY		BS EN/EN61000-4-5	Level 4. 4KV/Line-Earth : Level 3. 2KV/Line-Li				
EMC IMMUNITY	Surge						
EMC IMMUNITY	Surge Conducted	BS EN/EN61000-4-6	Level 3				
EMC IMMUNITY	Surge		Level 4, 4KV/Line-Earth ; Level 3, 2KV/Line-Lit Level 3 Level 4 >95% dip 0.5 periods, 30% dip 25 period >95% interruptions 250 periods				
EMC IMMUNITY	Surge Conducted Magnetic Field Voltage Dips and Interruptions	BS EN/EN61000-4-6 BS EN/EN61000-4-8	Level 3 Level 4 >95% dip 0.5 periods, 30% dip 25 period >95% interruptions 250 periods				
	Surge Conducted Magnetic Field Voltage Dips and Interruptions	BS EN/EN61000-4-6 BS EN/EN61000-4-8 BS EN/EN61000-4-11	Level 3 Level 4 >95% dip 0.5 periods, 30% dip 25 period >95% interruptions 250 periods				
MTBF DIMENSION PACKING	Surge Conducted Magnetic Field Voltage Dips and Interruptions 121.9K hrs min. Telcordia SR-332 (Be 540*424*83.5mm (L*W*H) 25Kg; 1pcs/25Kg/2.82CUFT	BS EN/EN61000-4-6 BS EN/EN61000-4-8 BS EN/EN61000-4-11	Level 3 Level 4 >95% dip 0.5 periods, 30% dip 25 period >95% interruptions 250 periods (25°C)				
	CURRENT (factory default) CURRENT RANGE RATED POWER FULL POWER VOLTAGE RANGE RIPPLE & NOISE (max.) Note.2 VOLTAGE ADJ. RANGE VOLTAGE TOLERANCE Note.3 LINE REGULATION LOAD REGULATION SETUP, RISE TIME HOLD UP TIME (Typ.) VOLTAGE RANGE FREQUENCY RANGE POWER FACTOR (Typ.) EFFICIENCY (Typ.) Note.7 AC CURRENT (Typ.) INRUSH CURRENT (Typ.) LEAKAGE CURRENT OVERLOAD OVER VOLTAGE OVER TEMPERATURE CURRENT SHARING OUTPUT VOLTAGE PROGRAMMABLE REMOTE ON-OFF CONTROL ALARM SIGNAL OUTPUT WORKING TEMP. WORKING TEMP. W	DC VOLTAGE (factory default) 115∨ CURRENT (factory default) 130A CURRENT RANGE 0 ~ 130A RATED POWER 14950W FULL POWER VOLTAGE RANGE 115 ~ 138V RIPPLE & NOISE (max.) Note.2 1Vp-p VOLTAGE ADJ. RANGE 90 ~ 138V VOLTAGE TOLERANCE Note.3 ± 1.0% LINE REGULATION ± 0.5% LOAD REGULATION ± 0.5% SETUP, RISE TIME 3000ms, 200ms at full load HOLD UP TIME (Typ.) 16ms 230VAC/400VAC at 75% load VOLTAGE RANGE 3# 3W/△ 196~305VAC or 3# 4W/Y 340 FREQUENCY RANGE 47 ~ 63Hz POWER FACTOR (Typ.) ≥ 0.98/230VAC(400VAC)/≥ 0.97/277VAC EFFICIENCY (Typ.) Note.7 93% AC CURRENT (Typ.) LEAKAGE CURRENT (Typ.) 150A/230VAC(3 # 3-wire / △) 100× 107% of rated current Protection type : Constant current limiting, 0VER VOLTAGE 145 ~ 166V OVER VOLTAGE Adjustment of constant current limiting, 0VER VOLTAGE Adjustment of constant current limiting, 0VER TEMPERATURE Adjustment	DC VOLTAGE (factory default) 115V 230V CURRENT (factory default) 130A 64.8A CURRENT RANGE 0 - 130A 0 - 69A RATED POWER 14950W 14904W FULL POWER VOLTAGE RANGE 115 - 138V 216 - 260V RIPPLE & NOISE (max.) Note2 IVp-p 2Vp-p VOLTAGE ADJ. RANGE 0 - 138V 170 - 260V ULR REGULATION ± 0.5% ± 1.0% LINR REGULATION ± 0.5% ± 0.5% SETUP, RISE TIME 3000ms, 200ms at full load 10ms / 230VAC/400VAC at full load VOLTAGE RANGE 3# 3M/196-305VAC or 3 # 4W/Y 340-530VAC FREQUENCY RANGE POWER RACTOR (Typ.) 45A/230VAC(3 # 3-wire / △) 26A/400VAC(3 # 4-wire / Y) ILRUSH CURRENT (Typ.) 45A/230VAC(3 # 3-wire / △) 26A/400VAC(3 # 4-wire / Y) ILRUSH CURRENT (Typ.) 45A/230VAC(3 # 3-wire / △) 26A/400VAC(3 # 4-wire / Y) ILRUSH CURRENT (Typ.) 45A/230VAC(3 # 3-wire / △) 26A/400VAC(3 # 4-wire / Y) ILRUSH CURRENT (Typ.) 45A/230VAC(3 # 3-wire / △) 26A/400VAC(3 # 4-wire / Y) ILRUSH CURRENT (Typ.) 45A/230VAC(3 # 3-				



15KW 3 ϕ 4W Input With High Voltage Output



















Fig 5.1

(2)Open collector output {DC-OK2-GND, DC-OK2) ; (AC-FAIL2-GND, AC-FAIL2) ; (OTP2, OTP2-GND) ; (FAN-FAIL2, FAN-FAIL2-GND)} An external voltage source is required for this function that is shown in Fig 5.2. These signals are isolated from output. The maximum sink current is 10mA and the maximum external voltage is 20V (there is a built-in 24V zener diode in inner circuitry).





6.Current Sharing

- RST-15K has the built-in active current sharing function and can be connected in parallel, up to 2 units, to provide higher output power as exhibited below :
- X The voltage difference among each output should be minimized that less than 0.2V is required.
- % The total output current must not exceed the value determined by the following equation.
- Maximum output current at parallel operation=(The rated current per unit)x(Number of unit)x0.95
- X When the total output current is less than 5% of the total rated current, or say (5% of Rated current per unit) × (Number of unit) the current shared among units may not be fully balanced.



 \bigcirc CS+, CS- and RC+, RC- are connected mutually in parallel.







1	15				
<u>۲۰</u> ۰		Mating Housing HRS DF11-16DS or equivalent Terminal HRS DF11-**SC or equivalent			
<u> </u>		Terminal HRS DF IT- SC of equivalent			
2	16				
in No.	Function	Description			
1	DC-OK1	Alarm signal of DC-OK. Normally open contact. "Short" when the PSU turns on. Relay contact rating(maximum) is 30V/1A resistive.			
2	AC-FAIL1	Alarm signal of AC-fail. Normally open contact. "Short" when the PSU input voltage is too low. Relay contact rating(maximum) is 30V/1A resistive.			
3	DC-OK1-GND	Alarm signal of DC-OK. Normally open contact. "Short" when the PSU turns on. Relay contact rating(maximum) is 30V/1A resistive.			
4	AC-FAIL1-GND	Alarm signal of AC-fail. Normally open contact. "Short" when the PSU input voltage is too low. Relay contact rating(maximum) is 30V/1A resistive.			
5	DC-OK2	Alarm signal of DC-OK. Open collector signal. Low when the PSU turns on. The maximum sink current is 10mA and the maximum external voltage is 20V.			
6	AC-FAIL2	Alarm signal of AC fail. Open collector signal. Low when the PSU input voltage is too low. The maximum sink current is 10mA and the maximum external voltage is 20V.			
7	DC-OK2-GND	Alarm signal of DC-OK. Open collector signal. Low when the PSU turns on. The maximum sink current is 10mA and the maximum external voltage is 20V.			
8	AC-FAIL2-GND	Alarm signal of AC fail. Open collector signal. Low when the PSU input voltage is too low. The maximum sink current is 10mA and the maximum external voltage is 20V.			
9	OTP1	Alarm signal of OTP. Normally open contact. "Short" when the PSU over temperature protection occurs. Relay contact rating(maximum) is 30V/1A resistive.			
10	FAN-FAIL2	Alarm signal of fan fail. Open collector signal. Low when the internal fan fails. The maximum sink current is 10mA and the maximum external voltage is 20V.			
11	OTP1-GND	Alarm signal of OTP. Normally open contact. "Short" when the PSU over temperature protection occurs. Relay contact rating(maximum) is 30V/1A resistive.			
12	FAN-FAIL2-GND	Alarm signal of fan fail. Open collector signal. Low when the internal fan fails. The maximum sink current is 10mA and the maximum external voltage is 20V.			
13	OTP2	Alarm signal of OTP. Open collector signal. Low when the PSU over temperature protection occurs. The maximum sink current is 10mA and the maximum external voltage is 20V.			
14	FAN-FAIL1	Alarm signal of fan fail. Normally open contact. "Short" when the internal fan fails. Relay contact rating(maximum) is 30V/1A resistive.			
15	OTP2-GND	Alarm signal of OTP. Open collector signal. Low when the PSU over temperature protection occurs. The maximum sink current is 10mA and the maximum external voltage is 20V.			
16	FAN-FAIL1-GND	Alarm signal of fan fail. Normally open contact. "Short" when the internal fan fails. Relay contact rating(maximum) is 30V/1A resistive.			

% Control Pin No. Assignment (CN25) : HRS DF11-08DP-2DS or equivalent

1 7	-		
n m m m		Mating Housing	HRS DF11-08DS or equivalent
		Terminal	HRS DF11-**SC or equivalent
2 8			

Function	Description			
12V-AUX	Auxiliary voltage output, 11.4~12.6V, referenced to pin 2,4(GND-AUX). Only for remote on-off control & Alarm signal. The maximum load current is 0.1A. This output is not controlled by the "Remote ON/OFF" function.			
GND-AUX	xiliary voltage output GND. e signal return is isolated from the output terminals (+V & -V).			
RC+	The output can be turned ON-OFF in association with RC+ and RC			
RC-				
	12V-AUX GND-AUX RC+			



℁LED Status Indicators

LED	Description
Green(LED1)	LED on when output voltage is OK
Red(LED2)	LED on when any protection occurs

XAC Input Terminal Pin No. Assignment (TB1)

Pin No.	Assignment	Pin No.	Assignment	Diagram	Maximum mounting torque
1	AC/L1	4	AC/N2		
2	AC/N1	5	AC/L3		18Kgf-cm
3	AC/L2	6	AC/N3		

XDIP Switch Position Assignment(DIP-SW): Please refer to the Function Manual.

Pin No.	Assignment	Diagram	
1	Overload Protection (OLP)	1 2 3	
2	Output Current Programming (PC)		
3	Output Voltage Programming (PV)	OFF DIP-SW PIN3:PV	

Installation Manual

Please refer to : http://www.meanwell.com/manual.html