


LFPAK33

shrinking the power footprint


The LFPAK33 brings Nexperia's **robust and reliable copper clip technology** to the Power33 (3.3 mm x 3.3 mm) footprint

Compact Footprint




- › Ultra-compact footprint - 10.9 mm²
- › Ultra-low height <1 mm
- › Footprint >80 % smaller than DPAK

Ultra Low On-Resistance




- › 6.3mΩ @ 40V
- › Copper clip technology
- › Ultra-low package resistance

Reliable & Manufacturable



- › High board level reliability
- › Easy optical inspection
- › Robust solder joints



High Current Rating



- › Best-in-class current rating
- › Up to 70 A per device
- › High transient robustness

LFLPAK33 Product Range

Product Name	V _{DS} [max] (V)	Gate Level	R _{DS(on)} [max] @ V _{GS} = 10 V (mΩ)	R _{DS(on)} [max] @ V _{GS} = 5 V (mΩ)	I _o [max] @ 25°C (A)	R _{th(j-mb)} [max] (K/W)
BUK9M5R2-30E	30	LL		5.2	70	1.89
BUK9M6R6-30E	30	LL		6.6	70	2
BUK9M10-30E	30	LL		10	59	2.75
BUK9M17-30E	30	LL		17	39	3.4
BUK7M6R3-40E	40	SL	6.3		70	1.89
BUK9M7R2-40E	40	LL		7.2	70	1.89
BUK7M8R0-40E	40	SL	8		70	2
BUK9M9R1-40E	40	LL		9.1	66	2
BUK7M10-40E	40	SL	10		60	2.43
BUK9M11-40E	40	LL		11	56	2.43
BUK7M12-40E	40	SL	12		52	2.75
BUK9M14-40E	40	LL		14	48	2.75
BUK7M21-40E	40	SL	21		35	3.4
BUK9M24-40E	40	LL		24	31	3.4
BUK7M45-40E	40	SL	45		21	4.8
BUK9M52-40E	40	LL		52	19	4.8
BUK7M9R9-60E	60	SL	9.9		60	1.89
BUK9M12-60E	60	LL		12	54	1.89
BUK7M12-60E	60	SL	12		54	2
BUK9M15-60E	60	LL		15	49	2
BUK7M15-60E	60	SL	15		46	2.43
BUK9M19-60E	60	LL		19	40	2.43
BUK7M19-60E	60	SL	19		39	2.75
BUK9M24-60E	60	LL		24	34	2.75
BUK7M33-60E	60	SL	33		26	3.4
BUK9M42-60E	60	LL		42	23	3.4
BUK7M42-60E	60	SL	42		21	4.17
BUK9M53-60E	60	LL		53	19	4.17
BUK7M67-60E	60	SL	67		16	4.8
BUK9M85-60E	60	LL		85	14	4.8
BUK7M17-80E	80	SL	17		43	1.89
BUK7M22-80E	80	SL	22		38	2
BUK9M23-80E	80	LL		23	37	1.89
BUK7M27-80E	80	SL	27		32	2.43
BUK9M28-80E	80	LL		28	34	2
BUK9M35-80E	80	LL		35	28	2.43
BUK9M34-100E	100	LL		34	28	1.89
BUK9M43-100E	100	LL		43	26	2
BUK9M120-100E	100	LL		120	12	3.4
BUK9M156-100E	100	LL		156	10	4.17

© 2017 Nexperia B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Date of release:

January 2017