


molex

AVNET[®] ABACUS



Molex
antenna portfolio

Molex antennas for the Smart Home

Intelligent and integrated smart home systems are bringing next generation connected devices into multiple consumer markets. Avnet Abacus offers an extensive portfolio of high performance Molex antennas for use across a broad spectrum of wireless applications in the Smart Home, as well as for industrial, medical and automotive markets.

Molex incorporates the latest innovative technology into its antenna portfolio which includes Bluetooth/Wi-Fi, GNSS, Combo, Cellular and NFC.

FURTHER RESOURCES




Learn how to bring the future home with Molex and view the on-demand webinar 'Antenna design considerations for a Smart Home' by visiting avnet-abacus.eu/molex

Content

Bluetooth/Wi-Fi antennas	4-5
GNSS antennas	6
Combo antennas (Wi-Fi, GPS, ISM, cellular...)	7
Cellular antennas	8
Ultra wide band (UWB) antennas	9
Industrial, scientific and medical (ISM) antennas	10
Near field communications (NFC) antennas	11
Molex antenna portfolio	12-13



Bluetooth/Wi-Fi antennas (1 of 2)

SERIES	146153		146187		204281	
Name	2.4/5 GHz balanced flex antenna with center-fed cable		2.4/5 GHz balanced pcb antenna with center-fed cable		2.4/5 GHz balanced flex antenna with side-fed cable	
Size	34.90mm x 9.00mm		40.95mm x 9.00mm		35.00mm x 11.00mm	
Cable length	50, 100, 150, 200, 250, 300mm		50, 100, 150, 200, 250, 300mm		50, 100, 150, 200, 250, 300mm	
Material	Flexible		PCB		Flexible	
Antenna type	Dipole-type, balanced		Dipole-type, balanced		Dipole-type, balanced	
Frequency range	2.4 to 2.5 GHz	5.15 to 5.85 GHz	2.4 to 2.5 GHz	5.15 to 5.85 GHz	2.4 to 2.5 GHz	5.15 to 5.85 GHz
Return loss	<-10 dB		-10 dB		<-10 dB	
Peak gain	3.0 dBi	4.0 dBi	3.2 dBi	4.5 dBi	2.0 dBi	3.3 dBi
Total radiation efficiency	>75%	>75%	>80%	>75%	>65%	>68%
Polarisation	Linear		Linear		Linear	
Input impedance	50 ohms		50 ohms		50 ohms	
Product image						

Note: Performance values above are based on 100mm cable





Bluetooth/Wi-Fi antennas (2 of 2)

SERIES	146175		47948	203006		
Name	2.4/5 GHz Wi-Fi SMT chip antenna		2.4 GHz Wi-Fi SMT chip antenna	2.4/5 GHz ceramic SMT antenna		
Size	3.00 x 5.00 x 4.00mm		3.00 x 3.00 x 4.00mm	3.20 x 1.60 x 1.10mm		
PCB clearance	4.00 x 6.00mm		4.00 x 4.00mm	4.00 x 6.00mm		
Material	LDS-MID		LDS-MID	Ceramic		
Antenna type	Inverted F-Antenna (IFA)		Monopole	Loop		
Frequency range	2.4 to 2.5 GHz	5.15 to 5.85 GHz	2.4 to 2.5 GHz	2.4 GHz	2.4 to 2.5 GHz	5.15 to 5.85 GHz
Return loss	<-6 dB		<-7 dB	-10 dB	-5 dB	
Peak gain	3.0 dBi	4.2 dBi	3.0 dBi	2.3 dBi	2.1 dBi	1.5 dBi
Total radiation efficiency	>70%		>70%	>70%	>60%	>55%
Polarisation	Linear		Linear	Linear		
Input impedance	50 ohms		50 ohms	50 ohms		
Product Image						

GNSS antennas

Part No.	146235			146216			146168	204286			204283		
Name	Helix GPS antenna			RHCP MID GPS antenna			RHCP ceramic GPS antenna	GPS/BEIDOU/GLONASS ceramic antenna			Low-profile GNSS ceramic antenna		
Size	3.00 x 5.00 x 4.00mm			11.80 x 11.55 x 6.00mm			25.00 x 25.00 x 4.00mm	25.00 x 25.00 x 4.00mm			3.20 x 1.60 x 1.10mm		
PCB clearance	4.00 x 6.00mm			No PCB clearance			No PCB clearance	No PCB clearance			5.00 x 6.00mm		
Material	LDS-MID			LDS-MID			Ceramic	Ceramic			Ceramic		
Antenna type	Monopole			Planar inverted-F antenna (PIFA)			Patch	Patch			Loop		
Frequency range	1561 ±5 MHz	1575 ±5 MHz	1602 ±5 MHz	1561 ±5 MHz	1575 ±5 MHz	1602 ±5 MHz	1.575 GHz	1561 ±5 MHz	1575 ±5 MHz	1602 ±5 MHz	1561 ±5 MHz	1575 ±5 MHz	1602 ±5 MHz
Return loss	<-8 dB			<-10 dB			<-15 dB	<-10 dB			<-8 dB	<-10 dB	<-8 dB
Peak gain	0.7 dBi	1.1 dBi	1.1 dBi	0.7 dBi	0.7 dBi	1.5 dBi	5.5 dBi	5.2 dBi	5.4 dBi	5.6 dBi	1.5 dBi	2.0 dBi	1.6 dBi
Total radiation efficiency	>50%	>55%	>50%	>55%	>57%	>60%	>75%	>70%	>70%	>75%	>60%	>65%	>60%
Polarisation	Elliptic			RHCP			RHCP	Elliptic			Linear		
Axial ratio	<6.0 dB			<3.0 dB			<3.0 dB	<13.0 dB	<7 dB	<12 dB	-		
Input impedance	50 ohms			50 ohms			50 ohms	50 ohms			50 ohms		

Combo antennas (Wi-Fi, GPS, ISM and cellular)


SERIES	146186				146220				203007					201932		
Name	GPS/Wi-Fi combo balanced flexible antenna				GPS/Wi-Fi combo balanced pcb antenna				2.4/5 GHz, combo GPS/Wi-Fi ceramic antennas					2.4/5 GHz & 900 MHz triple band antenna		
Size	53.00 x 18.00mm				53.50 x 16.60mm				3.20 x 1.60 x 1.10mm					20.00 x 5.00 x 4.00mm		
Material	Flexible				PCB				Ceramic					Ceramic		
Antenna type	Dipole-type, balanced				Dipole-type, balanced				Loop					IFA		
PCB clearance	N.A.				N.A.				6.20 x 8.00mm					30.00 x 6.00mm		
Cable length	50, 100, 150, 200, 250, 300mm				50, 100, 150, 200, 250, 300mm				N.A.					N.A.		
Frequency range	1.575 to 1.602 GHz	2.4 to 2.5 GHz	5.15 to 5.85 GHz	3 to 6 GHz	1.575 to 1.602 GHz	2.4 to 2.5 GHz	5.15 to 5.85 GHz	3GHz to 6 GHz	1.561 GHz	1.575 GHz	1.602 GHz	2.4 to 2.5 GHz	5.15 to 5.85 GHz	900 to 924 MHz	2.4 to 2.5 GHz	5.15 to 5.85 GHz
Return loss	<-10 dB				<- 8 dB				<-6 dB	<-10 dB	<-6 dB	<-6 dB	<-5.5 dB	<- 5 dB	<- 6 dB	<- 5 dB
Peak gain	3.0 dBi	3.0 dBi	4.0 dBi	4.7 dBi	2.4 dBi	2.9 dBi	3.8 dBi	3.5 dBi	0.9 dBi	1.0 dBi	0.3 dBi	0.6 dBi	1.0 dBi	0.7 dBi	4.2 dBi	4.5 dBi
Total radiation efficiency	>70%	>75%	>70%	>80%	>82%	>80%	>83%	>78%	>55%	>55%	>50%	>55%	>50%	>40%	>65%	>55%
Polarisation	Linear				Linear				Linear					Linear		
Input impedance	50 ohms				50 ohms				50 ohms					50 ohms		
Product image																

Note: Performance values above are based on 100mm cable



Cellular antennas

PART NO.	105263		146185		146200		204774	
Name	Multi(6)-band cellular flexible antenna		Multi-band combo cellular Wi-Fi flexible antenna		Full LTE SMT antenna		791 to 960 and 1710 to 2700 MHz	
Size	106.6 x 13.00mm		84.00 x 15mm		40.00 x 5.00 x 5.00mm		33.00 x 6.00 x 3.00mm	
Material	Flexible		Flexible		Ceramic		Ceramic	
Antenna type	Dipole-type, balanced		Dipole-type, balanced		SD type with MobliquA technology		Coupler	
PCB clearance	N.A.		N.A.		50.00 x 10.00mm		43.00 x 9.00mm	
Cable length	50, 100, 150, 200, 250, 300mm		50, 100, 150, 200, 250, 300mm		N.A.		N.A.	
Frequency range	824 to 960 MHz	1.71 to 2.7 GHz	824 to 960 MHz	1.7 to 2.7 GHz	698 to 960 MHz	1.71 GHz to 2.7 GHz	790 to 960 MHz	1.71 to 2.17 GHz
Return loss	<-6 dB		<-4 dB	<-4 dB	<-5 dB		<-6 dB	
Peak gain	2.3 dBi	3.1 dBi	1.4 dBi	3 dBi	1.1 dBi	4.5 dBi	0.6 dBi	4.8 dBi
Total radiation efficiency	>66%	>60%	>60%	>65%	>60%	>70%	>50%	>70%
Polarisation	Linear		Linear		Linear		Linear	
Input impedance	50 ohms		50 ohms		50 ohms		50 ohms	
Product image								

Ultra wide band (UWB) antennas

SERIES	146184
Name	Ultra wide band PCB antenna
Size	47.00 x 17.6mm
Material	PCB
Antenna type	Dipole, balanced
Cable length	100mm
Frequency range	3 GHz to 6 GHz
Return loss	<-6 dB
Total radiation efficiency	70%
Peak gain	4.5 dBi
Polarisation	Linear
Input impedance	50 ohms
Product image	

Industrial, scientific and medical (ISM) antennas

SERIES	105262		204287
Name	868/915 MHz ISM standalone antenna		433 MHz ISM antenna
Size	79.00 x 10.00mm		90.00 x 40.00mm
Material	Flexible		Flexible
Antenna type	MobliquA technology, balanced		Dipole-type, balanced
Cable length	50, 100, 150, 200, 250, 300mm		50, 100, 150, 200, 250, 300mm
Frequency range	863 - 870 MHz	902 - 928 MHz	433 MHz
Return loss	<-6 dB		<-10 dB
Total radiation efficiency	50%	66%	>56% (50mm cable), >55% (100mm cable), >54% (150mm cable), >52% (200mm), >51% (250mm), >50% (300mm)
Peak gain	0.4 dBi (100mm cable) 0.3 dBi (150mm cable) 0.2 dBi (200mm cable)	1.4 dBi (100mm cable) 1.3 dBi (150mm cable) 1.2 dBi (200mm cable)	0.8 dBi (50mm cable), 0.7 dBi (100mm cable), 0.6 dBi (150mm cable), 0.5 dBi (200mm), 0.4 dBi (250mm), 0.3 dBi (300mm)
Polarisation	Linear		Linear
Input impedance	50 ohms		50 ohms
Product image			

Near field communication (NFC) antennas

SERIES	146236	
Name	NFC antenna without ferrite	NFC antenna with ferrite
Sizes	15.00 x 15.00mm 23.00 x 27.00mm 34.00 x 46.00mm 45.00 x 55.00mm	
Material	FPC	FPC + ferrite
Antenna type	Near field coupling	
Frequency range	13.56 MHz	
Inductor @ 13.56 MHz	2.11 μ H 2.09 μ H 2.76 μ H 2.59 μ H	3.32 μ H 3.22 μ H 4.25 μ H 3.92 μ H
Product image		

Molex antenna portfolio

Category	Protocol	Series no.	Operating frequency		Antenna type		SMD mounting type	PCB/flexible antenna mounting		Cable alignment with antenna		Cable diameter (mm)	Cable length (mm)		Connector type	
			2.4 GHz	5.0 GHz	Embedded	Internal cable assembly		PCB corner	PCB centre-edge	Peel-and-stick	Screw mounting		Parallel	Perpendicular	50/100/150 200/250/300 200/250/300	Custom length
BT/Wi-Fi	Zigbee Bluetooth BLE Thread Wi-Fi	47948	•		•		•									
		146175	•	•	•		•									
		203006	•	•	•			•								
		146153	•	•		•			•		•	•	•	•	•	•
		204281	•	•		•			•		•	•	•	•	•	•
		146187	•	•		•				•		•	•	•	•	•

Category	Protocol	Series No.	Operating frequency (MHz)			Antenna type		Polarisation			Mounting		Antenna size (mm)
			1561	1575	1602	Passive	Active	RHCP	Elliptic	Linear	SMD	Pin & adhesive	
GNSS	GPS Glonass Beidou Gallieo	146235	•	•	•	•		•		•		3x5x4	
		146216	•	•	•	•		•		•		11.8x11.55x6	
		146168		•		•		•			•	25x25x4	
		204286	•	•	•	•		•			•	25x25x4	
		204283	•	•	•	•				•	•	3.2x1.6x1.1	

Category	Protocol	Series no.	Operating frequency (MHz)			Antenna type		Flexible antenna mounting	Cable alignment w/ antenna		Cable diameter (mm)	Cable length (mm)		Connector type	
			433	868	915	Embedded	Internal cable assembly		Peel-and-stick	Parallel		Perpendicular	1.13	100/ 150/ 200	50/ 250/ 300
ISM	Sigfox Neul Z-wave LoRa	105262		•	•		•	•	•	•	•		•	•	
		204287	•				•	•	•	•	•	•	•	•	

Molex antenna portfolio

Category	Protocol	Series no.	Operating frequency (MHz)				Antenna type		SMD mounting type	Flex antenna mounting	Cable alignment w/ antenna		Cable diameter (mm)	Cable length (mm)		Connector type	
			698 to 960	790 to 960	824 to 960	1710 to 2700	Embedded	Internal cable assembly			PCB end	Peel-and-stick		Parallel	Perpendicular	100/150/200	50/250/300
Cellular	2G/3G/4G	105263			•	•		•		•		•	•			•	•
	LTE	146185			•	•		•		•		•	•			•	•
	LPWA (Cat-M1/NB1)	146200	•			•	•										
		204774		•		•	•										

Category	Protocol	Series no.	Operating frequency band		Antenna type		PCB/Flex antenna mounting	Cable alignment with antenna		Cable diameter (mm)	Cable length (mm)		Connector type					
			2.4/5 GHz+GPS	2.4/5 GHz+900 MHz	Embedded	Internal cable assembly		Peel-and-stick	Screw mounting		Parallel	Perpendicular	50, 100, 150, 200, 250, 300	Custom length	UFL MHF1	Custom		
Combo	Wi-Fi + GPS; Wi-Fi + 900 MHz	146186	•			•	•			•	•	•	•	•	•	•	•	
		146220	•			•		•		•	•	•	•	•	•	•	•	
		203007	•			•												
		201932		•		•												

Category	Protocol	Series no.	Frequency	Antenna type		Flex antenna mounting	Cable alignment with antenna		Cable diameter (mm)	Cable length (mm)		Connector type		
			3 to 6 GHz	Embedded	Internal cable assembly		Peel-and-stick	Parallel		Perpendicular	50, 100, 150, 200, 250, 300	Custom length	UFL MHF1	Custom
UWB	UWB	146184	•		•	•	•		•	•	•	•	•	•

Category	Protocol	Series no.	Frequency 13.56 MHz	With ferrite	Without ferrite	With cable	Without cable	Size (mm)
			NFC	NFC	146236	•	•	•

Offices

AUSTRIA

Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642 0
Fax: +43 1 86642 250
wien@avnet-abacus.eu

BELARUS

c/o Avnet Abacus Russia
Office 26, Building 2
10 Korovinskoye Shosse,
127486 Moscow
Phone: +7 (495) 737 3689
Fax: +7 (495) 737 3686
belarus@avnet-abacus.eu

BELGIUM

De Kleetlaan 3
1831 Diegem
Phone: +32 2 227 2000
diegem@avnet-abacus.eu

BULGARIA

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642 0
Fax: +43 1 86642 250
bulgaria@avnet-abacus.eu

CROATIA

c/o Avnet Abacus Slovenia
Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
croatia@avnet-abacus.eu

CZECH REPUBLIC

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
praha@avnet-abacus.eu

DENMARK

Knudlundvej 24
DK-8653 Them
Phone: +45 86 84 84 84
Fax: +45 86 84 82 44
them@avnet-abacus.eu

Lyskær 9, DK-2730 Herlev
Phone: +45 86 84 84 84
Fax: +45 43 29 37 00
herlev@avnet-abacus.eu

EGYPT

Canan Residence
Hendem Cad.
No:54 Ofis A2
Serifali Umraniye Istanbul
TR - 34775 Turkiye
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
egypt@avnet-abacus.eu

ESTONIA

Aida 5,
EE-80011 Pärnu
Phone: +372 56637737
paernu@avnet-abacus.eu

FINLAND

Pihatörmä 1 B
FI-02240 Espoo
Phone: +358 (0) 207 499 220
Fax: +358 (0) 207 499 240
espool@avnet-abacus.eu

FRANCE

Immeuble Carnot Plaza
14 Avenue Carnot
91349 Massy Cedex, Paris
Phone: +33 (0) 1 6447 2929
Fax: +33 (0) 1 6447 9150
paris@avnet-abacus.eu

8 chemin de la Terrasse
Bat D 1er étage
31500 Toulouse
Phone: +33 (0) 5 6247 4787
Fax: +33 (0) 5 6247 4761
toulouse@avnet-abacus.eu

35 avenue des Peupliers
Les Peupliers2
35510 Cesson
Phone: +33 (0) 2 9983 7720
Fax: +33 (0) 2 9983 4829
rennes@avnet-abacus.eu

Parc Club du Moulin à Vent
Bât 10, 33 rue du Dr. G Lévy
F-69693 Vénissieux Cedex,
Lyon
Phone: +33 (0) 4 7877 1370
Fax: +33 (0) 4 7877 1391
lyon@avnet-abacus.eu

GERMANY

Englische Str. 27
D - 10587 Berlin
Phone: +49 (0) 30 790 997 0
Fax: +49 (0) 30 790 997 51
berlin@avnet-abacus.eu

Industriestr. 26
D-76297 Stutensee
Phone: +49 (0)7249 910 149
Fax: +49 (0)7249 910 177
stutensee@avnet-abacus.eu

Wilhelmstr. 1, D-59439
Holzwickede / Dortmund
Phone: +49 (0) 2301 2959 27
Fax: +49 (0) 2301 2959 29
dortmund@avnet-abacus.eu

Oehleckerring 9a - 13
22419 Hamburg
Phone: +49 (0) 40 608 23 59 0
Fax: +49 (0) 40 608 23 59 20
hamburg@avnet-abacus.eu

Gruber Str. 60c-60d
D-85586 Poing / Munich
Phone: +49 (0) 8121 777 03
Fax: +49 (0) 8121 777 531
muenchen@avnet-abacus.eu

Lina-Ammon-Str. 19 b
D-90471 Nürnberg
Phone: +49 (0) 911 244 250
Fax: +49 (0) 911 244 25 25
nuernberg@avnet-abacus.eu

Gutenbergstr. 15
D-70771 Leinfelden-
Echterdingen / Stuttgart
Phone: +49 (0) 711 78260 02
Fax: +49 (0) 711 78260 333
stuttgart@avnet-abacus.eu

Gaußstraße 10
D-31275 Lehrte
Phone: +49 (0) 5132 5099 0
Fax: +49 (0) 5132 5099 76
lehrte@avnet-abacus.eu

GREECE

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
greece@avnet-abacus.eu

HUNGARY

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
budapest@avnet-abacus.eu

IRELAND

c/o Avnet Abacus Bolton
Oceanic Building
Waters Meeting Road
Bolton BL1 8SW
Phone: +44 (0)1204 547170
Fax: +44 (0)1204 547171
bolton@avnet.eu

ISRAEL

Avnet Components Israel Ltd.
P.O. Box 48 Tel-Mond, 4065001
Phone: 972-9-7780280
Fax: 972-3-760-1115
avnet.israel@avnet.com

ITALY

Via Manzoni 44
I-20095 Cusano Milanino
(Milano)
Phone: +39 02 660 921
Fax: +39 02 66092 332
milano@avnet-abacus.eu

Viale dell'industria 23
I-35129 Padova
Phone: +39 049 7800 381
Fax: +39 049 7730 36
padova@avnet-abacus.eu

Via Zoe Fontana 220
I-00131 Roma
Phone: +39 06 4123 1952
Fax: +39 06 4192 618
roma@avnet-abacus.eu

Via Scaglia Est, 31/33
41126 Modena
Phone: +39 059 34891
Fax: +39 059 344993
modena@avnet-abacus.eu

Via Panciatichi 40/11
I-50127 Firenze
Phone: +39 055 436 1928
Fax: +39 055 428 8810
firenze@avnet-abacus.eu

LATVIA

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
latvia@avnet-abacus.eu

LITHUANIA

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
lithuania@avnet-abacus.eu

NETHERLANDS

Stadionstraat 2, 6th fl.
NL-4815 NG Breda
Phone: +31 (0) 76 57 22 300
Fax: +31 (0) 76 57 22 303
breda@avnet-abacus.eu

NORWAY

Ryensvingen 3 B
N-0680 Oslo
Phone: +47 (0) 22 70 76 60
Fax: +47 (0) 22 70 76 61
oslo@avnet-abacus.eu

POLAND

Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
wroclaw@avnet-abacus.eu

PORTUGAL

Tower Plaza, Rot. Eng. Edgar
Cardoso, 23, Pl. 14, Sala E
PT-4400-676 Vila Nova
de Gaia
Phone: +351 223 779502
Fax: +351 223 779503
portugal@avnet-abacus.eu

ROMANIA

c/o Avnet Abacus Slovenia
Dunajska Cesta 159
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
romania@avnet-abacus.eu

RUSSIA

Office 31, Building 2
10 Korovinskoye Shosse
127486 Moscow
Phone: +7 (495) 737 3689
Fax: +7 (495) 737 3686
Moscow@avnet-abacus.eu

SERBIA

c/o Avnet Abacus Slovenia
Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
serbia@avnet-abacus.eu

SLOVAKIA

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
slovakia@avnet-abacus.eu

SLOVENIA

Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
ljubljana@avnet-abacus.eu

SOUTH AFRICA

Ground Floor, Forrest House
Belmont Office Park
Belmont Road, Rondebosch
7700, Cape Town
Phone: +27 (0) 21 689 4141
Fax: +27 (0) 21 686 4709
sales@avnet.co.za

202 Chelmsford, 2nd Floor
Nelson Road, Essex Gardens,
Westville, 3629, Durban
Phone: +27 (0) 31 266 8104
Fax: +27 (0) 31 266 1891
sales@avnet.co.za

Block 3, Pinewood Office Park
33 Riley Road
Woodmead, 2191
Sandton, Johannesburg
Phone: +27 (0) 11 319 8600
Fax: +27 (0) 11 319 8650
sales@avnet.co.za

SPAIN

NyN Tower, C/ Tarragona,
151-157, Floor 19
ES-08014 Barcelona
Phone: +34 (0) 93 327 85 50
Fax: +34 (0) 93 425 05 44
barcelona@avnet-abacus.eu

Plaza Zabalgane
12 Bajo Izda,
Galdakao / Vizcaya
ES -48960 Bilbao
Phone: +34 (0) 94 457 0044
Fax: +34 (0) 94 456 8855
bilbao@avnet-abacus.eu

C/Chile, 10 2ª Plta.
Oficina 229
ES -28290 Las Matas / Madrid
Phone: +34 (0) 913 72 7200
Fax: +34 (0) 916 36 9788
madrid@avnet-abacus.eu

SWEDEN

Löfströms Allé 5,
Sundbyberg, Box 1830,
SE-171 27 Solna
Phone: +46 (0) 858 746200
Fax: +46 (0) 858 746 001
stockholm@avnet-abacus.eu

Smörhålevägen 3
SE-43442 Kungsbäcka
Phone: +46 (0)8 58746 200
Fax: +46 (0)300 140 15
gothenburg@avnet-abacus.eu

SWITZERLAND

Bernstrasse 392
CH-8953 Dietikon
Phone: +41 (0) 43 322 49 90
Fax: +41 (0) 43 322 49 99
zurich@avnet-abacus.eu

TURKEY

Canan Residence
Hendem Cad.
No:54 Ofis A2
Serifali Umraniye Istanbul
TR - 34775 Turkiye
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
istanbul@avnet-abacus.eu

UK

First Floor, The Gatehouse
Gatehouse Road
Aylesbury, Bucks
HP19 8DB
Phone: +44 (0) 1296 678920
Fax: +44 (0) 1296 678939
aylesbury@avnet.eu

Building 5
Waltham Park
White Waltham
Maidenhead
Berkshire SL6 3TN
Phone: +44 (0)1628 512900
Fax: +44 (0)1628 512999
maidenhead@avnet.eu

Avnet House
Rutherford Close
Meadway,
Stevenage
Hertfordshire SG1 2EF
Phone: +44 (0)1438 788 500
Fax: +44 (0)1438 788 250
stevenage@avnet.eu

Oceanic Building
Waters Meeting Road
Bolton
BL1 8SW
Phone: +44 (0)1204 547170
Fax: +44 (0)1204 547171
bolton@avnet.eu

UKRAINE

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
ukraine@avnet-abacus.eu

All trademarks and logos are the property of their respective owners. This document provides a brief overview only, no binding offers are intended. No guarantee as to the accuracy or completeness of any information. All information is subject to change, modifications and amendments without notice. Printed on FSC certified paper.