

Series 293

3-in-1 Joystick, Optical Encoder & Pushbutton Switch

Description

- 4-Directional Joystick with Excellent Tactile Feedback
- Built-In Optical Encoder with 20 Positions
- Integrated Pushbutton Switch
- Joystick Operational Life up to 500k Activations in Each Direction
- Optical Encoder Rotational Life up to 1M Cycles
- Pushbutton Switch Operational Life up to 1M Activations
- Wide Operating Temperature Range: -40°C to 85°C
- Fully RoHS Compliant



The series 293 is a combined joystick, encoder and pushbutton switch solution from CTS Corporation. This 3-in-1 joystick offers excellent control in four directions, and the integrated optical encoder grants high precision and resolution with a total of 20 positions. The series 293 is ideal for controls in medical applications such as power wheelchair navigation, ultrasound scan control panels and patient positioning tables. It is also well-suited for industrial control units and remote controls for unmanned aerial vehicles e.g., drones.

Ordering Information

Series	Joystick	Encoder	Pushbutton Switch Function	Termination
293	4	20	1	0
	↓	↓	↓	↓
	Code		Code	
	Joystick		Push Switch	
	4		Function	
	4 Directions		1	
			With Push Switch	
		Code		Code
		Encoder		Termination
		20		0
		20 Positions (5P/R)		Connector
				1
				50mm Wire with Connector

Electrical Specifications



Parameter	Conditions & Remarks	Min	Nominal	Max	Unit
Encoder Function					
Input Voltage		4.75	5.0	5.25	V _{DC}
Input Current	5 V _{DC}			20	mA
Output Signal (High)		3.5			V _{DC}
Output Signal (Low)				1.0	V _{DC}
Sink Current		2.0			mA
Power Consumption				100	mW
Resolution	5				Pulses per Revolution
Joystick Function					
Input Current				5	mA
Output Signal (Neutral)		2.0	2.5	3.0	V _{DC}
Output Signal (High)		4.5			V _{DC}
Output Signal (Low)				0.5	V _{DC}
Switch Function					
Rating	5 V _{DC}		10		mA
Contact Resistance				10	Ω
Contact Bouncing		4 (make)		10 (break)	ms

Mechanical and Environmental




Encoder	Rotational Torque: 100 ± 50 gf · cm Click per Rotation: 20 Rotational Life: 1 Million Cycles
Joystick	Angle of Throw: 8° ± 2° Operation Force: 150 ± 75 gf Joystick Life: 500,000 Activations in Each Direction (X, Y)
Switch	Operation Force: 350 ± 150 gf Shaft Travel: 0.5 ± 0.2 mm Switch Life: 1 Million Activations
Others	Mounting Torque: 12 kgf · cm (maximum) Actuator Force: 2 kg (maximum) Shaft Pull-out Force: 10 kg (maximum) Shaft Push-out Force: 10 kg (maximum)
Operating Temperature:	-40°C to +85°C
Storage Temperature:	-50°C to +95°C
RoHS	Fully Compliant to RoHS Directive

29342011



(Unit: mm)



293S0002 — P/N
 136 24 A — DATE CODE
 SHIFT CODE
 YEAR CODE
 "24" FOR 2024
 DATE CODE
 136th DAY



RECOMMENDED PANEL CUT OUT




PIN ASSIGNMENT

Pin No.	Function
1	Joystick "X"
2	Joystick "Y"
3	Power "+5V"
4	Output "A"
5	Output "B"
6	Switch
7	Switch
8	GND


Output

• JOYSTICK




"Y High" defined by locating pin.

• PUSHBUTTON



• ENCODER Output Waveform



Position \ Output	A	B
1		
2	•	
3	•	•
4		•

• = High
Blank = Low

OUTPUT CIRCUITRY AND RECEIVING CIRCUITRY

